

Alternate Design Configurations

A wearer may prefer one progressive lens over another based on their expectations and visual demands. **USO Camber HD** progressive lenses can be configured for patients' lifestyles.

USO Camber HD | Near Vision




Ideal wearer: expert or novice progressive lens wearers who have visual demands that call for a larger more usable near area.

USO Camber HD | Distance Vision



Ideal wearer: expert or novice progressive lens wearers who have visual demands that call for a larger more usable distance area.

USO Camber HD | Intermediate Vision



Ideal wearer: first-time wearers, wearers who have experienced non-adapts with other progressive lenses, and those who have visual demands that call for a larger more usable intermediate area.

—— USO Camber HD progressive standard configuration

US OPTICAL
FASTEST LAB IN AMERICA!™

800-445-2773 • www.usoptical.com
6848 Ellicott Dr., East Syracuse, NY 13057



USO Camber HD Progressive Lenses

Fully personalized free-form
progressive lenses designed
with revolutionary technologies.

camber™
With IOT Intelligence

USO Camber HD Progressive Lenses

We live in a dynamic and ever-changing society. Our lives are fast paced, and the digital age is here to stay. **USO Camber HD** progressive lenses adapt to the demands of modern life. Their technology meets the visual needs of the most active presbyopes, who demand clear and stable vision, even when they're engaged in highly dynamic activities. **USO Camber HD** progressive lenses can be personalized for each wearer.

USO Camber HD progressive lenses incorporate **IOT Digital Ray-Path 2 Technology** and **Steady Plus Methodology**. With this methodology, the swim effect is significantly reduced. The optics and aesthetics of **USO Camber HD** progressive lenses are impossible to beat.

No lens is more advanced

USO Camber HD progressive lenses provide the wearer with an unbeatable visual experience: wide reading zones, improved peripheral vision, extended power range, more aesthetically pleasing lenses, and unbeatable near vision performance.

Ideal Wearer

Those looking for the best visual quality or who want the most innovative solutions. Digitally connected wearers looking for maximum visual comfort. Those who value the aesthetics of their finished lenses. Wearers with all types of prescription and addition powers, especially medium to high.



USO Camber HD | Standard Configuration

Features & Benefits

- Fully personalized dual-sided progressive lens
- Near, distance, & intermediate enhancements available
- Technologies: Camber™, IOT Digital Ray-Path 2, Steady Plus
- Optimized for accommodative object space
- Superior visual acuity
- Improved quality of vision in the near zone
- Improved aesthetics in many prescriptions
- Precise & comfortable focus for all working distances in any direction of gaze
- Near elimination of peripheral blur
- Superior visual quality for viewing digital devices
- Higher image stability for reduced swim effect
- Better performance in binocular vision at near & intermediate
- MFHs: 14, 15, 16, 17, & 18 mm or variable